



Qwik II Connector™, SC, OM1, Beige, for 250/900um, 25 per pack

Product Classification

Portfolio	CommScope®
Brand	OptiSPEED® Qwik
Product Series	Qwik II
Product Type	Fiber connector
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	OM1
Ferrule Geometry	Factory polished
Ferrule Material	Zirconia
Fiber Mode	Multimode

Dimensions

Compatible Cable Diameter, maximum	0.90 mm 0.04 in
Compatible Cable Diameter, minimum	0.25 mm 0.01 in
Length	50.20 mm 1.98 in

General Specifications

Interface	SC
Body Style	BTW
Interface Feature	Field Installable Mechanical splice
Color	Beige
Color, boot	Black
Package Quantity	25

Mechanical Specifications

Cable Retention Strength, maximum	1.00 lb @ 0 °
------------------------------------------	---------------

Optical Performance

Insertion Loss, typical	0.27 dB
--------------------------------	---------

Return Loss, minimum 20.0 dB

Optical Specifications

Optical Components Standard ANSI/TIA-568. 3-D

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2015

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system

