



1-5/8 EIA Coupling Element, O-Ring, screw-set

Product Classification

Product Type Coupling element

General Specifications

Interface 1-5/8 in EIA Flange
Includes O-rings | Screw set

Electrical Specifications

Connector Impedance 50 ohm
Operating Frequency Band 0 – 5200 MHz

Mechanical Specifications

Inner Contact Plating Silver

Dimensions

Height 41.50 mm | 1.63 in
Length 68.20 mm | 2.69 in
Weight 0.20 kg | 0.44 lb
Width 41.50 mm | 1.63 in

Standard Conditions

Attenuation, Ambient Temperature 20 °C | 68 °F
Average Power, Ambient Temperature 20 °C | 68 °F
Average Power, Inner Conductor Temperature 100 °C | 212 °F

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

