



6-1/8 EIA Coupling Element, O-Ring, screw-set

## Product Classification

**Product Type** Coupling element

## General Specifications

**Interface** 6-1/8 in EIA Flange  
**Includes** O-rings | Screw set

## Electrical Specifications

**Connector Impedance** 50 ohm  
**Operating Frequency Band** 1 – 5200 MHz

## Mechanical Specifications

**Inner Contact Plating** Silver

## Dimensions

**Height** 153.70 mm | 6.05 in  
**Length** 106.60 mm | 4.20 in  
**Weight** 0.80 kg | 1.76 lb  
**Width** 153.70 mm | 6.05 in

## Standard Conditions

**Attenuation, Ambient Temperature** 20 °C | 68 °F  
**Average Power, Ambient Temperature** 20 °C | 68 °F  
**Average Power, Inner Conductor Temperature** 100 °C | 212 °F

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

