

## HomeConnect® Non-Locking Terminator, parking port, brass



### Product Classification

<b>Brand</b>	HomeConnect®
<b>Product Type</b>	Terminator

### Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +60 °C (-40 °F to +140 °F)
<b>Safety Standard</b>	CE   EN 60728-4   SCTE

### Electrical Specifications

<b>Impedance</b>	75 ohm
<b>Operating Frequency Band</b>	5 – 2000 MHz
<b>Return Loss at Frequency Band, minimum</b>	20 dB @ 1700–2000 MHz   24 dB @ 1002–1700 MHz   25 dB @ 1002–1500 MHz   30 dB @ 5–1002 MHz

### General Specifications

<b>Device Type</b>	Non-locking terminator
<b>Parking Port</b>	Included

### Dimensions

<b>Contact Pin Diameter</b>	0.813 mm   0.032 in
<b>Contact Pin Diameter Tolerance</b>	±0.002 in

### Mechanical Specifications

<b>Material Type</b>	Brass
<b>Plating</b>	Nickel

### Packed Dimensions

<b>Carton Quantity</b>	1250
<b>Height</b>	190.50 mm   7.50 in
<b>Length</b>	330.20 mm   13.00 in
<b>Width</b>	241.30 mm   9.50 in
<b>Shipping Weight</b>	19.05 kg   42.00 lb

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU  
ISO 9001:2015

**Classification**

Compliant  
Designed, manufactured and/or distributed under this quality management system

