



Qwik II Connector™, LC, SM-UPC, Blue, for 0.25/0.9/2.0/3.0 mm, single pack

Product Classification

Portfolio	CommScope®
Brand	Qwik TeraSPEED®
Product Series	Qwik II
Product Type	Fiber connector
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	OS2
Ferrule Geometry	Factory polished
Ferrule Material	Zirconia
Fiber Mode	Singlemode

Dimensions

Compatible Cable Diameter, maximum	3.00 mm 0.12 in
Compatible Cable Diameter, minimum	0.25 mm 0.01 in

General Specifications

Interface	LC
Body Style	Universal
Interface Feature	Field Installable Mechanical splice UPC
Color	Blue
Color, boot	Black
Package Quantity	1

Optical Performance

Insertion Loss, typical	0.30 dB
Return Loss, minimum	45.0 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2015

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system

