



Qwik II Connector™, SC, SM-UPC, Blue, for 0.25/0.9/2.0/3.0 mm, single pack

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Brand</b>	Qwik   TeraSPEED®
<b>Product Series</b>	Qwik II
<b>Product Type</b>	Fiber connector
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Construction Materials

<b>Fiber Type</b>	OS2
<b>Ferrule Geometry</b>	Factory polished
<b>Ferrule Material</b>	Zirconia
<b>Fiber Mode</b>	Singlemode

## Dimensions

<b>Compatible Cable Diameter, maximum</b>	3.00 mm   0.12 in
<b>Compatible Cable Diameter, minimum</b>	0.25 mm   0.01 in

## General Specifications

<b>Interface</b>	SC
<b>Body Style</b>	Universal
<b>Interface Feature</b>	Field Installable   Mechanical splice   UPC
<b>Color</b>	Blue
<b>Color, boot</b>	Black
<b>Package Quantity</b>	1

## Optical Performance

<b>Insertion Loss, typical</b>	0.30 dB
<b>Return Loss, minimum</b>	45.0 dB

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU  
ISO 9001:2015

**Classification**

Compliant  
Designed, manufactured and/or distributed under this quality management system

