



Qwik-Fuse Connector, LC, OM3/OM4/OM5, Aqua, for 1.6/2.0 mm, 12 per pack

Product Classification

Portfolio	CommScope®
Brand	LazrSPEED® Qwik
Product Series	Qwik-Fuse
Product Type	Fiber connector
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	OM3 OM4 OM5, LazrSPEED® wideband
Ferrule Geometry	Factory polished
Ferrule Material	Zirconia
Fiber Mode	Multimode

Dimensions

Compatible Cable Diameter	1.6 mm 2.0 mm
----------------------------------	-----------------

General Specifications

Interface	LC
Body Style	Cordage
Interface Feature	Field Installable Fusion splice
Color	Aqua
Color, boot	Aqua
Package Quantity	12

Mechanical Specifications

Cable Retention Strength, maximum	5.08 lb @ 0 °
--	---------------

Optical Performance

Insertion Loss, maximum	0.25 dB
Insertion Loss, typical	0.10 dB
Return Loss, minimum	30.0 dB

Optical Specifications

Optical Components Standard

ANSI/TIA-568. 3-D | IEC 61753-1

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

