


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

© 2016 Commscope, INC. Confidential NOTICE: These drawings and specifications are the proprietary property of COMMSCOPE, INC. and may be used only for the specific purpose authorized in writing by COMMSCOPE, INC.

REVISONS		DATE	DWN	APVD
P	LTR	DESCRIPTION		
E		ECR-09-019359	31082009	MO MO
F		ECN 8000017738 - REBRANDING	22NOV2016	LS OV



LC CLIP SIDE MARK	SC CONN. MARK
A	B
B	A

NOTES:

- 1 ATTENUATION ≤ 0.3 dB, MEASURED AT 850 nm I.E.C. 61300-3-4 METHOD B
- 2 RETURN LOSS ≥ 30 dB, IN MATED CONDITION
- 3 FILLED OUT TEST RESULT SHEET SUPPLIED WITH EACH INDIVIDUALLY PACKED ASSEMBLY
- 4 BLANK LABEL
- 5 CABLE INFORMATION:
  - CORE DIAMETER: 50/125 μm
  - OUTER JACKET DIAMETER: 1.8x3.6 mm
  - OUTER JACKET COLOUR: AQUA
  - OUTER JACKET MATERIAL: LSZH
- 6 FOR LENGTHS < 60 cm SHORTER SLIT LENGTHS APPLY
- 7 SC DUPLEX CONNECTOR IS LEFT UNASSEMBLED AS SHOWN
- 8 INDIVIDUAL LENGTH DIFFERENCE ON SC SIDE ≤ 5 mm
- 9 ADDITIONAL ATTENUATION FOR LONG LEADS ACC. TO CUSTOMER DRAWING 1920435
- 10 DELIVERED ON A REEL IN A BOX

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" ( meter )
X-6536967-Y	XY.0
8-6536967-1	1.5 -0/+0.1
8-6536967-2	100.0 -0/+3.0
9-6536967-0	0.5 -0/+0.05
9-6536967-1	0.75 -0/+0.1
9-6536967-2	2.5 -0/+0.1

2	BLANK LABEL	4
1	SC DUPLEX CONNECTOR, MULTI MODE	3
1	LC DUPLEX CONNECTOR, MULTI MODE, BEIGE	2
L	FOCAB 1.8MZ OM3 50/125, AQUA LSZH	1
Qty	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN R. COOLEN 01AUG2007	<b>COMMSCOPE, INC.</b>  FOMM50 OM3 LEAD 1.8MZ LC DUPLEX - SC DUPLEX	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
CHK A. HENGELMOLEN 01AUG2007		A2	-	C=6536967	-	
APVD A. HENGELMOLEN 01AUG2007		WEIGHT	-	CUSTOMER DRAWING	SCALE	NTS
PRODUCT SPEC		APPLICATION SPEC	-	SHEET	1 OF 1	REV