


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © 2016 Commscope, INC. Confidential NOTED: these drawings and specifications are the proprietary property of COMMSCOPE, INC. and may be used only for the specific purpose authorized in writing by COMMSCOPE, INC.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
F		ECN 8000017776-REBRANDING	15-DEC-16	SC	JV



NOTES:

- INSERTION LOSS ≤ 0.3 dB, MEASURED AGAINST REF. CONN.
- RETURN LOSS ≥ 45 dB, MATED
- TUNED CONNECTOR
- BLANK LABEL
- CABLE:
 - 9/125/900 μ m
 - CABLE: 2,5mmx5,1mm
 - CABLE COLOUR: YELLOW
 - TIGHT
 - OUTER SHEATH MATERIAL: LSZH
- INFO ON CABLE LABEL:
 - UNIQUE SERIAL NUMBER
 - CommScope PARTNUMBER
 - P.O. NUMBER
 - INSERTION LOSS AND RETURN LOSS AT 1310nm LENGTH DIFFERENCE 5 mm MAX.

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-6348260-Y	XY,0
8-6348260-2	2,25 +0,10/-0

CUSTOMER REFERENCE

Item	Description	Qty
6	CABLE LABEL	9
4	DUST CAP , NATURAL CLEAR	8
2	SC DUPLEX HOUSING, BEAM HALF, BLUE	7
2	SC DUPLEX HOUSING, RETENTION PLATE, BLUE	6
4	SC PLUG ASSY, SINGLEMODE, BEIGE, 125 μ m	5
4	CRIMP EYELET	4
2	SC STRAIN RELIEF, RED	3
2	SC STRAIN RELIEF, BLACK	2
L	DUAL CABLE 2.5mm, SM, LSZH, YELLOW	1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DW: R. COOLEN	01 JUL 05	COMMSCOPE, INC.
CHK: ARIE HENGELMOLEN	26 OCT 05	
APVD: ARIE HENGELMOLEN	26 OCT 05	
NAME: ARIE HENGELMOLEN		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC: -
0 PLC \pm -	1 PLC \pm -	APPLICATION SPEC: -
1 PLC \pm -	2 PLC \pm -	SIZE: A2
2 PLC \pm -	3 PLC \pm -	CAGE CODE: -
3 PLC \pm -	4 PLC \pm -	DRAWING NO: C=6348260
4 PLC \pm -	ANGLES \pm -	RESTRICTED TO: -
MATERIAL: -	FINISH: -	WEIGHT: -
CUSTOMER DRAWING		SCALE: 1:1
		SHEET: 1 of 1
		REV: F