



Copper Patch Cord, 4P AMP-TWIST, category 7A, S/FTP, white, 10 m

Product Classification

Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord
Regional Availability	Asia Australia/New Zealand EMEA

Dimensions

Cord Length	10.00 m 32.81 ft
Diameter Over Jacket	5.59 mm 0.22 in

Electrical Specifications

ANSI/TIA Category	7A
--------------------------	----

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Cable Type	S/FTP (shielded)
Interface, connector A	4P AMP-TWIST Plug
Interface, connector B	4P AMP-TWIST plug
Jacket Color	White
Pairs, quantity	4

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU
---------------	-----------------

Classification	Compliant
-----------------------	-----------

