



## ION® Power Distribution Unit with limited current

### Product Classification

<b>Brand</b>	ION®
<b>Product Type</b>	Power distribution unit

### General Specifications

<b>Fan Connector Interface</b>	4-pin header, male (4.2 mm pitch)
<b>Note</b>	Detailed Product Specifications are available. Please contact your local CommScope representative.
<b>Output Connector Interface</b>	2-pin header, male (7.62 mm pitch)

### Electrical Specifications

<b>Electrical Safety Standard</b>	EN 60950
<b>Fans Supported, quantity</b>	7
<b>Outputs Supported, total, quantity</b>	17

### Supervision And Control

<b>General Alarm</b>	Integrated into management system
----------------------	-----------------------------------

### Dimensions

<b>Depth</b>	343.40 mm   13.52 in
<b>Height</b>	44.45 mm   1.00 HE
<b>Width</b>	482.60 mm   19.00 in
<b>Net Weight</b>	4.50 kg   9.92 lb

### Packed Dimensions

<b>Depth</b>	530.0 mm   20.9 in
<b>Height</b>	230.0 mm   9.1 in
<b>Width</b>	590.0 mm   23.2 in
<b>Shipping Weight</b>	5.50 kg   12.13 lb

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

