



iPatch® M4200i 24 Port UTP Intelligent Universal Modular Panel without Modules

Product Classification

| | |
|------------------------------|---|
| Portfolio | SYSTIMAX® |
| Brand | imVision® iPatch® |
| Product Type | RJ45 patch panel |
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |

Dimensions

| | |
|---------------|----------------------|
| Depth | 25.40 mm 1.00 in |
| Height | 44.45 mm 1.75 in |
| Weight | 0.68 kg 1.50 lb |
| Width | 482.60 mm 19.00 in |

Electrical Specifications

| | |
|--------------------------|--------|
| ANSI/TIA Category | 6 6A |
|--------------------------|--------|

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Flammability Rating | UL 94 V-0 |
| Operating Temperature | -5 °C to +50 °C (+23 °F to +122 °F) |
| Relative Humidity | Up to 95%, non-condensing |
| Safety Standard | ACMA CE cUL UL |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |

General Specifications

| | |
|------------------------------|--|
| Intelligence Type | iPatch® enabled |
| Total Ports, quantity | 24 |
| Cable Type | Unshielded |
| Color | Black |
| Includes | Cable management bar Four #12-24 dog point mounting screws Information outlet removal tool Instruction sheet Panel Two #12 washers Two #12-24 screws |
| Package Quantity | 1 |
| Rack Units | 1.0 |

Mechanical Specifications

| | |
|----------------------|---|
| Panel Style | Straight |
| Material Type | Acrylonitrile butadiene styrene (ABS) Polycarbonate |

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

