



360G2 Cassette 12 LC Singlemode Blue with Pigtails iPatch Ready

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cassette with pigtails
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Construction Materials

<b>Fiber Type</b>	G.652.D and G.657.A1 , TeraSPEED®   OS2
<b>Total Fibers, quantity</b>	12

## Dimensions

<b>Depth</b>	119.38 mm   4.70 in
<b>Height</b>	30.48 mm   1.20 in
<b>Pigtail Length</b>	1.5 m   4.9 ft
<b>Width</b>	91.44 mm   3.60 in

## Environmental Specifications

<b>Safety Standard</b>	UL
------------------------	----

## General Specifications

<b>Interface, front</b>	LC
<b>Adapter Color</b>	Blue
<b>Intelligence Type</b>	iPatch® ready
<b>Interface Feature, front</b>	Standard
<b>Package Quantity</b>	1
<b>Total Ports, quantity, front</b>	12

## Optical Performance

<b>Insertion Loss, typical</b>	0.30 dB
<b>Return Loss, minimum</b>	55.0 dB

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU  
ISO 9001:2015

### Classification

Compliant  
Designed, manufactured and/or distributed under this quality management system



## Included Products

860278613 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, blue, 1.5 m

- 760095596 | X-TB-8W-BL-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
- 760211201 | X-TB-8G-BL-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber

860278621 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, orange, 1.5 m

- 760095604 | X-TB-8W-OR-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
- 760211219 | X-TB-8G-OR-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber

860278639 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, green, 1.5 m

- 760095612 | X-TB-8W-GR-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode

860278647 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, brown, 1.5 m

- 760095620 | X-TB-8W-BR-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode

860278654 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, slate, 1.5 m

- 760095638 | X-TB-8W-SL-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode

860278662 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, white, 1.5 m

- 760095646 | X-TB-8W-WH-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode

860278670 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, red, 1.5 m

- 760095653 | X-TB-8W-RD-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode

# 760109496 | 360G2 Cassette 12-LC-SM-BL-Pigtails

---

- 860278688 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, black, 1.5 m
- 760095661 | X-TB-8W-BK-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
  - 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
- 860278696 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, yellow, 1.5 m
- 760038570 | X-TB-8W-YL-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
  - 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
  - 760200568 | X-TB-8G-YL-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
- 860278704 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, violet, 1.5 m
- 760095679 | X-TB-8W-VI-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
  - 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
- 860278712 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, rose, 1.5 m
- 760095687 | X-TB-8W-RS-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
  - 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
- 860278720 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, aqua, 1.5 m
- 760095695 | X-TB-8W-AQ-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
  - 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
- 760049809 | SFA-LC12-BL-SHUTTERED — TeraSPEED® LC Multiport Shuttered Adapter, Blue, Single Pack