

InstaPATCH® 360 SinglemodeTS TAP Module, 50:50, 24 ports



## Product Classification

|                              |   |
|------------------------------|---|
| <b>Portfolio</b>             | SYSTIMAX®   |
| <b>Brand</b>                 | InstaPATCH® 360   |
| <b>Product Type</b>          | Fiber module  |
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |

## Construction Materials

|                               |                            |
|-------------------------------|----------------------------|
| <b>Fiber Type</b>             | G.652.D and G.657.A1   OS2 |
| <b>Total Fibers, quantity</b> | 24                         |

## Dimensions

|               |                     |
|---------------|---------------------|
| <b>Depth</b>  | 165.10 mm   6.50 in |
| <b>Height</b> | 27.94 mm   1.10 in  |
| <b>Width</b>  | 91.44 mm   3.60 in  |

## Environmental Specifications

|                        |    |
|------------------------|----|
| <b>Safety Standard</b> | UL |
|------------------------|----|

## General Specifications

|                                     |                            |
|-------------------------------------|----------------------------|
| <b>Interface, front</b>             | LC                         |
| <b>Total Ports, quantity, front</b> | 24                         |
| <b>Interface Feature, front</b>     | Standard                   |
| <b>Color, front</b>                 | Blue                       |
| <b>Adapters, quantity, front</b>    | 24                         |
| <b>Data Module Type</b>             | TAP (Traffic Access Point) |
| <b>Intelligence Type</b>            | iPatch® ready              |
| <b>Shuttered</b>                    | No                         |
| <b>Interface, rear</b>              | MPO Male                   |
| <b>Adapters, quantity, rear</b>     | 4                          |
| <b>Interface Feature, rear</b>      | Reduced footprint          |
| <b>Color, rear</b>                  | Gray   Red                 |
| <b>Package Quantity</b>             | 1                          |

## Optical Performance

**Insertion Loss, maximum** 4.27 dB

**Tap Insertion Loss, maximum** 4.64 dB

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

ISO 9001:2015

### Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

