



RJ45 Patch Cord, category 6, UTP, plug to open end, white, 15 m

## Product Classification

|                              |                                     |
|------------------------------|-------------------------------------|
| <b>Portfolio</b>             | NETCONNECT®                         |
| <b>Product Type</b>          | Twisted pair patch cord             |
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA |

## Dimensions

|                             |                    |
|-----------------------------|--------------------|
| <b>Cord Length</b>          | 15.00 m   49.21 ft |
| <b>Diameter Over Jacket</b> | 5.59 mm   0.22 in  |

## Electrical Specifications

|                          |   |
|--------------------------|---|
| <b>ANSI/TIA Category</b> | 6 |
|--------------------------|---|

## Environmental Specifications

|                              |                                     |
|------------------------------|-------------------------------------|
| <b>Environmental Space</b>   | Low Smoke Zero Halogen (LSZH)       |
| <b>Operating Temperature</b> | -20 °C to +60 °C (-4 °F to +140 °F) |

## General Specifications

|                               |                    |
|-------------------------------|--------------------|
| <b>Cable Type</b>             | U/UTP (unshielded) |
| <b>Interface, connector A</b> | RJ45 plug          |
| <b>Interface, connector B</b> | Unterminated       |
| <b>Jacket Color</b>           | White              |
| <b>Pairs, quantity</b>        | 4                  |

## Regulatory Compliance/Certifications

|               |                 |
|---------------|-----------------|
| <b>Agency</b> | RoHS 2011/65/EU |
|---------------|-----------------|

|                       |           |
|-----------------------|-----------|
| <b>Classification</b> | Compliant |
|-----------------------|-----------|

