



Copper Patch Cord, 4P AMP-TWIST, category 7A, S/FTP, white, 0.5 m

Product Classification

| | |
|------------------------------|-------------------------------------|
| Portfolio | NETCONNECT® |
| Product Type | Twisted pair patch cord |
| Regional Availability | Asia Australia/New Zealand EMEA |

Dimensions

| | |
|-----------------------------|-------------------|
| Cord Length | 0.50 m 1.64 ft |
| Diameter Over Jacket | 5.59 mm 0.22 in |

Electrical Specifications

| | |
|--------------------------|----|
| ANSI/TIA Category | 7A |
|--------------------------|----|

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Environmental Space | Low Smoke Zero Halogen (LSZH) |
| Operating Temperature | -20 °C to +60 °C (-4 °F to +140 °F) |
| Storage Temperature | -40 °C to +85 °C (-40 °F to +185 °F) |

General Specifications

| | |
|-------------------------------|-------------------|
| Cable Type | S/FTP (shielded) |
| Interface, connector A | 4P AMP-TWIST Plug |
| Interface, connector B | 4P AMP-TWIST plug |
| Jacket Color | White |
| Pairs, quantity | 4 |

Regulatory Compliance/Certifications

| | |
|---------------|-----------------|
| Agency | RoHS 2011/65/EU |
|---------------|-----------------|

| | |
|-----------------------|-----------|
| Classification | Compliant |
|-----------------------|-----------|

