



ION®-B Series Extension Unit for TDD 2500 Band Applications

Product Classification

Brand	ION®-B
Product Type	Extension unit

General Specifications

Note	CrossBandCoupler included; Jumper (1dB loss maximum)
Power Type	High

Electrical Specifications

License Band	TDD 2500
Voltage Range	+100 to +240 Vac

Electrical Specifications Rx (Uplink)

Operating Frequency Band	2496 – 2690 MHz (TDD 2500)
---------------------------------	----------------------------

Electrical Specifications Tx (Downlink)

Operating Frequency Band	2496 – 2690 MHz (TDD 2500)
---------------------------------	----------------------------

Mechanical Specifications

Communications Port Interface	QMA Female
Communications Port, quantity	8