



Undercarpet Conference Room Kit, category 6, 3-conductor, black

- Provides services for power and communications (4 ports of communications and 2 duplex power receptacles)
- Reduces cost of installation, no core drilling required
- Yields a more aesthetically pleasing and cleaner installation than power poles
- Provides one circuit of power to two duplex receptacles in a compact, durable floor mounted outlet
- Provides four ports of any combination of voice or data on Cat 5e or Cat 6 cable to RJ45 jacks in a compact, durable floor mounted outlet
- Transition boxes can be easily retrofitted in place of existing power and communications wall outlets

Product Classification

Product Series	Undercarpet
Product Type	Conference room kit
Regional Availability	North America

Electrical Specifications

ANSI/TIA Category	6
Current Rating, maximum	20.00 A
Signal Configuration	Data Power
Voltage Rating, maximum	300.00 Vac

Environmental Specifications

Environmental Space	Indoor
Safety Standard	UL

General Specifications

Cable Type	FCC
Color	Black
Grounding Connection	Standard
Insulation Material	PVC
Package Quantity	1
Pairs, quantity	4
Total Ports, quantity	4

Mechanical Specifications

Conductor Gauge, solid	12 AWG
-------------------------------	--------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

