



## ION®-U High Power Extension Unit for EDD 800 Band Application

### Product Classification

<b>Brand</b>	ION®-U
<b>Product Type</b>	Extension unit

### General Specifications

<b>Note</b>	Detailed Product Specifications are available. Please contact your local CommScope representative.
<b>Power Type</b>	High

### Electrical Specifications

<b>License Band</b>	EDD 800
<b>Voltage Range</b>	+100 to +240 Vac

### Output Power Per Antenna Port

<b>Note</b>	* 66 dBc @ 2 and 4 carriers; 63 dBc @ 8 carriers; 60 dBc @ 16 carriers   ** For carrier bandwidth < 5 MHz output power shall be reduced by 2 dB
-------------	---

### Electrical Specifications Rx (Uplink)

<b>Input ICP-3, specific</b>	-13 dBm (EDD 800 MAIN), ICP-3 optimized   -17 dBm (EDD 800 MAIN), NF optimized
<b>Operating Frequency Band</b>	832 – 862 MHz (EDD 800)

### Electrical Specifications Tx (Downlink)

<b>Operating Frequency Band</b>	791 – 821 MHz (EDD 800)
---------------------------------	-------------------------