



ION®-B Series Extension Unit for WCS2300 Band Applications

Product Classification

Brand	ION®-B
Product Type	Extension unit

General Specifications

Note	CrossBandCoupler included; Jumper (1dB loss maximum)
Power Type	High

Electrical Specifications

License Band	WCS 2300
Voltage Range	-60 to -38 Vdc

Electrical Specifications Rx (Uplink)

Operating Frequency Band	2305 – 2315 MHz (WCS 2300)
---------------------------------	----------------------------

Electrical Specifications Tx (Downlink)

Operating Frequency Band	2350 – 2360 MHz (WCS 2300)
---------------------------------	----------------------------

Mechanical Specifications

Communications Port Interface	QMA Female
Communications Port, quantity	2