

imVision® imPower™



Product Classification

Portfolio	SYSTIMAX®
Brand	imPower™ imVision®
Product Type	Network controller accessory
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

General Specifications

Color	Black
Package Quantity	1

Dimensions

Depth	127.00 mm 5.00 in
Height	43.18 mm 1.70 in
Width	76.20 mm 3.00 in
Weight	0.05 kg 0.10 lb

Mechanical Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate
----------------------	---

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	0 °C to +50 °C (+32 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Safety Standard	C-tick CE cUL GOST KC

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU
---------------	-----------------

Classification	Compliant
-----------------------	-----------

