



ION®-B Series Extension Unit for AWS 1700 Band Applications

## Product Classification

<b>Brand</b>	ION®-B
<b>Product Type</b>	Extension unit

## General Specifications

<b>Note</b>	CrossBandCoupler included; Jumper (1dB loss maximum)
<b>Power Type</b>	High

## Electrical Specifications

<b>License Band</b>	AWS 1700
<b>Voltage Range</b>	+85 to +264 Vac

## Electrical Specifications Rx (Uplink)

<b>Operating Frequency Band</b>	1710 – 1780 MHz (AWS 1700)
---------------------------------	----------------------------

## Electrical Specifications Tx (Downlink)

<b>Operating Frequency Band</b>	2110 – 2180 MHz (AWS 1700)
---------------------------------	----------------------------

## Mechanical Specifications

<b>Communications Port Interface</b>	QMA Female
<b>Communications Port, quantity</b>	8