



ION®-U High Power Remote Unit for DCS 1800 and IMT 2100 Band Applications

Product Classification

Brand	ION®-U
Product Type	Remote unit

General Specifications

Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Power Type	High

Electrical Specifications

License Band	DCS 1800 IMT 2100
Voltage Range	+100 to +240 Vac

Electrical Specifications Rx (Uplink)

Operating Frequency Band 1710 – 1785 MHz (DCS 1800) | 1920 – 1980 MHz (IMT 2100)

Electrical Specifications Tx (Downlink)

Operating Frequency Band 1805 – 1880 MHz (DCS 1800) | 2110 – 2170 MHz (IMT 2100)