



Copper Patch Cord, 2P AMP-TWIST to RJ45, S/FTP, LZSH, stranded, white, 15 m

## Product Classification

|                              |                                     |
|------------------------------|-------------------------------------|
| <b>Portfolio</b>             | NETCONNECT®                         |
| <b>Product Type</b>          | Twisted pair patch cord             |
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA |

## Dimensions

|                    |                    |
|--------------------|--------------------|
| <b>Cord Length</b> | 15.00 m   49.21 ft |
|--------------------|--------------------|

## Electrical Specifications

|                          |    |
|--------------------------|----|
| <b>ANSI/TIA Category</b> | 6A |
|--------------------------|----|

## Environmental Specifications

|                            |                               |
|----------------------------|-------------------------------|
| <b>Environmental Space</b> | Low Smoke Zero Halogen (LSZH) |
|----------------------------|-------------------------------|

## General Specifications

|                               |                   |
|-------------------------------|-------------------|
| <b>Cable Type</b>             | S/FTP (shielded)  |
| <b>Interface, connector A</b> | RJ45 plug         |
| <b>Interface, connector B</b> | 2P AMP-TWIST plug |
| <b>Jacket Color</b>           | White             |
| <b>Package Quantity</b>       | 1                 |
| <b>Pairs, quantity</b>        | 2                 |

## Mechanical Specifications

|                       |          |
|-----------------------|----------|
| <b>Conductor Type</b> | Stranded |
|-----------------------|----------|

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

