

G2 ULL Multimode OM5 MPO-24 Distribution Module, 1x24F MPO unpinned to 24F LC Lime Green, Method B Enhanced, iPatch Ready



Product Classification

| | |
|------------------------------|---|
| Portfolio | SYSTIMAX® |
| Brand | SYSTIMAX ULL |
| Product Type | Fiber module |
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |

Construction Materials

| | |
|-------------------------------|--------------------------|
| Fiber Type | OM5, LazrSPEED® wideband |
| Total Fibers, quantity | 24 |

Dimensions

| | |
|---------------|---------------------|
| Depth | 113.28 mm 4.46 in |
| Height | 24.64 mm 0.97 in |
| Width | 95.00 mm 3.74 in |

Environmental Specifications

| | |
|--------------------------------|-----------------|
| Qualification Standards | TIA/EIA-568-C.3 |
| Safety Standard | cUL US 1863 |

General Specifications

| | |
|-------------------------------------|---------------|
| Interface, front | LC |
| Total Ports, quantity, front | 24 |
| Interface Feature, front | Standard |
| Color, front | Lime green |
| Adapters, quantity, front | 12 |
| Data Module Type | G2 |
| Intelligence Type | iPatch® ready |
| Shuttered | No |
| Interface, rear | MPO Unpinned |
| Adapters, quantity, rear | 1 |
| Interface Feature, rear | Key up |

Color, rear Lime green
Package Quantity 1

Optical Performance

Insertion Loss, maximum 0.35 dB

Regulatory Compliance/Certifications

| Agency | Classification |
|-----------------|--|
| RoHS 2011/65/EU | Compliant |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

