



ION®-M High Power Remote Unit for DCS 1800 Band Applications

Product Classification

Brand	ION®-M
Product Type	Remote unit

General Specifications

Minimum Software Requirement	ION-M SW V6.50
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Power Type	High

Electrical Specifications

License Band	DCS 1800
Voltage Range	+100 to +240 Vac

Electrical Specifications Rx (Uplink)

Flatness, inband link	±1.dB
Operating Frequency Band	1710 – 1785 MHz (DCS 1800)

Electrical Specifications Tx (Downlink)

Operating Frequency Band	1805 – 1880 MHz (DCS 1800)
---------------------------------	----------------------------