



ION®-M High Power Remote Unit for EDD 800 and IMT 2600 Band Applications

Product Classification

Brand	ION®-M
Product Type	Remote unit

General Specifications

Minimum Software Requirement	ION-M SW V6.50
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Power Type	High

Electrical Specifications

License Band	EDD 800 IMT 2600
Voltage Range	+100 to +240 Vac

Electrical Specifications Rx (Uplink)

Flatness, inband link	±1.dB
Operating Frequency Band	2500 – 2570 MHz (IMT 2600) 832 – 862 MHz (EDD 800)

Electrical Specifications Tx (Downlink)

Operating Frequency Band	2620 – 2690 MHz (IMT 2600) 791 – 821 MHz (EDD 800)
---------------------------------	--