



ION®-M High Power Remote Unit with Extension Port for DCS 1800, IMT 2100, and IMT 2600 Band Applications

## Product Classification

**Brand** ION®-M  
**Product Type** Remote unit

## General Specifications

**Minimum Software Requirement** ION-M SW V6.50  
**Note** Detailed Product Specifications are available. Please contact your local CommScope representative.  
**Power Type** High

## Electrical Specifications

**License Band** DCS 1800 | IMT 2100 | IMT 2600  
**Voltage Range** +100 to +240 Vac

## Electrical Specifications Rx (Uplink)

**Operating Frequency Band** 1710 – 1785 MHz (DCS 1800) | 1920 – 1980 MHz (IMT 2100) | 2500 – 2570 MHz (IMT 2600)

## Electrical Specifications Tx (Downlink)

**Operating Frequency Band** 1805 – 1880 MHz (DCS 1800) | 2110 – 2170 MHz (IMT 2100) | 2620 – 2690 MHz (IMT 2600)