



PIM-free Multifunction Adapter for SnapTak Hangers

- Snaps into 3/4" holes to provide 1 inch standoff
- Threads into 3/8" & 1/2" bolts & U-bolts to launch hangers
- Snaps between SnapTak hangers to provide 360 degree hanger rotation
- For patents see www.cs-pat.com

Product Classification

Brand	PIM-guard
Product Type	Adapter

Dimensions

Height	26.00 mm 1.02 in
Length	29.00 mm 1.14 in
Width	29.00 mm 1.14 in

General Specifications

Adapter Type	Stand-off adapter
Color	Black
Material Type	Engineered plastic
Ordering Note	CommScope® standard product in the United States and Canada
Package Quantity	10

Mechanical Specifications

Environmental Strength Capability	Double cable weight
Maximum Loading	Triple stack for hangers SSH-47, SSH-710, & SSH-1014, & SSH-1416
Mounting	1/2 in threads 3/4 in through hole 3/8 in threads
UV Resistance, minimum with no degradation	=1000 hours
Vibration Survival	=4 hours at resonant frequency

Packed Dimensions

Height	17.0 cm 6.7 in
Length	10.0 cm 3.9 in
Shipping Weight	0.15 kg 0.33 lb
Width	13.0 cm 5.1 in

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

