



Angle Adapter, compact, M10 tapped hole

Product Classification

Product Type Adapter

Dimensions

Inside Length	15.88 mm 0.63 in
Inside Width	15.88 mm 0.63 in
Outside Length	46.99 mm 1.85 in
Outside Width	38.10 mm 1.50 in

General Specifications

Adapter Type	Angle adapter
Material Type	Stainless steel
Ordering Note	CommScope® non-standard product
Package Quantity	10

Mechanical Specifications

Installation Torque, maximum	13.0 ft lb
Installation Torque, minimum	11.0 ft lb
Material Thickness	2.972 mm 0.117 in
Maximum Loading	Double stack, 1-5/8 in cable
Mounting	M10 tapped hole

Packed Dimensions

Height	14.0 cm 5.5 in
Length	11.0 cm 4.3 in
Shipping Weight	1.59 kg 3.50 lb
Width	14.0 cm 5.5 in

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

243684-M

RoHS 2011/65/EU
ISO 9001:2015
China RoHS SJ/T 11364-2014

Compliant
Designed, manufactured and/or distributed under this quality management system
Above Maximum Concentration Value (MCV)

