



Angle Adapter, compact 3/8 in tapped hole

## Product Classification

**Product Type** Adapter

## Dimensions

**Inside Length** 15.88 mm | 0.63 in  
**Inside Width** 15.88 mm | 0.63 in  
**Outside Length** 46.99 mm | 1.85 in  
**Outside Width** 38.10 mm | 1.50 in

## General Specifications

**Adapter Type** Angle adapter  
**Material Type** Stainless steel  
**Ordering Note** CommScope® standard product in Mexico, Central America, and South America  
**Package Quantity** 10

## Mechanical Specifications

**Installation Torque, maximum** 13.0 ft lb  
**Installation Torque, minimum** 11.0 ft lb  
**Material Thickness** 2.972 mm | 0.117 in  
**Maximum Loading** Double stack, 1-5/8 in cable  
**Mounting** 3/8 in tapped hole

## Packed Dimensions

**Height** 14.0 cm | 5.5 in  
**Length** 11.0 cm | 4.3 in  
**Shipping Weight** 1.32 kg | 2.91 lb  
**Width** 14.0 cm | 5.5 in

## Regulatory Compliance/Certifications

**Agency** **Classification**

# 243684

---

RoHS 2011/65/EU  
ISO 9001:2015  
China RoHS SJ/T 11364-2014

Compliant  
Designed, manufactured and/or distributed under this quality management system  
Above Maximum Concentration Value (MCV)

