

# 31768A

Angle Adapter, standard, 3/8 in tapped hole



## Product Classification

**Product Type** Adapter

## Dimensions

<b>Inside Length</b>	22.23 mm   0.88 in
<b>Inside Width</b>	22.23 mm   0.88 in
<b>Outside Length</b>	44.96 mm   1.77 in
<b>Outside Width</b>	49.81 mm   1.96 in

## General Specifications

<b>Adapter Type</b>	Angle adapter
<b>Material Type</b>	Stainless steel
<b>Ordering Note</b>	CommScope® standard product in the United States and Canada
<b>Package Quantity</b>	10

## Mechanical Specifications

<b>Installation Torque, maximum</b>	15.0 ft lb
<b>Installation Torque, minimum</b>	11.0 ft lb
<b>Material Thickness</b>	4.191 mm   0.165 in
<b>Maximum Loading</b>	Triple stack, 1-5/8 in cable
<b>Mounting</b>	3/8 in tapped hole

## Packed Dimensions

<b>Height</b>	14.2 cm   5.6 in
<b>Length</b>	10.2 cm   4.0 in
<b>Shipping Weight</b>	2.33 kg   5.14 lb
<b>Width</b>	14.2 cm   5.6 in

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

**Classification**

Compliant

Designed, manufactured and/or distributed under this quality management system

Below Maximum Concentration Value (MCV)

