

# 1316MCLICK



Miniature Click-on Hanger for 13–16 mm cable - Hardware Sold Separately

## Product Classification

**Product Type** Hanger kit

## Dimensions

<b>Nominal Size</b>	1/2 in   3/8 in
<b>Compatible Diameter, maximum</b>	16.256 mm   0.640 in
<b>Compatible Diameter, minimum</b>	13.716 mm   0.540 in
<b>Height</b>	38.00 mm   1.50 in
<b>Length</b>	55.00 mm   2.17 in
<b>Width</b>	25.00 mm   0.98 in

## Electrical Specifications

<b>DTF Effect</b>	0.1 dB
<b>Return Loss Effect</b>	0.1 dB

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

## General Specifications

<b>Hanger Type</b>	Click-on hanger
<b>Cables per Hanger</b>	2
<b>Color</b>	Black
<b>Material Type</b>	Engineered plastic
<b>Maximum Stack Height</b>	3
<b>Ordering Note</b>	CommScope® standard product in Europe, the Middle East, and Africa   CommScope® standard product in the United States and Canada
<b>Package Quantity</b>	10

## Mechanical Specifications

<b>Mounting</b>	M8 through hole
<b>UV Resistance, minimum with no degradation</b>	≥100 hours exposure in accelerated UV life chamber

# 1316MCLICK

---

**Vibration Survival** ≥4 hours at resonant frequency  
**Environmental Strength Capability** Double cable weight

## Packed Dimensions

**Height** 44.7 cm | 17.6 in  
**Length** 17.7 cm | 7.0 in  
**Shipping Weight** 0.05 kg | 0.12 lb  
**Width** 39.4 cm | 15.5 in

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Below Maximum Concentration Value (MCV)



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power