



Universal Snap-in Hanger for 7/8 in corrugated, smoothwall, and braided coaxial cable

## Product Classification

<b>Brand</b>	I-Line
<b>Product Type</b>	Hanger kit

## Dimensions

<b>Nominal Size</b>	7/8 in
<b>Compatible Diameter, maximum</b>	30.988 mm   1.220 in
<b>Compatible Diameter, minimum</b>	26.670 mm   1.050 in
<b>Height</b>	41.00 mm   1.61 in
<b>Length</b>	71.00 mm   2.80 in
<b>Width</b>	37.00 mm   1.46 in

## Electrical Specifications

<b>DTF Effect</b>	0.1 dB
<b>Return Loss Effect</b>	0.1 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

## General Specifications

<b>Hanger Type</b>	Snap-in hanger
<b>Cables per Hanger</b>	1
<b>Color</b>	Silver
<b>Material Type</b>	Stainless steel
<b>Ordering Note</b>	CommScope® non-standard product
<b>Package Quantity</b>	10

## Mechanical Specifications

**Corrosion Resistance, minimum with no degradation** ≥500 hours in salt spray chamber

**Mounting** 3/4 in drilled cable ladder

**Vibration Survival** ≥4 hours at resonant frequency

**Environmental Strength Capability** Double cable weight

## Packed Dimensions

**Height** 17.0 cm | 6.7 in

**Length** 10.0 cm | 3.9 in

**Shipping Weight** 0.44 kg | 0.96 lb

**Width** 13.0 cm | 5.1 in