



Universal Snap-in Hanger for 2-1/4 in corrugated coaxial cable

OBSOLETE

This product was discontinued on: September 1, 2015

Product Classification

| | |
|---------------------|------------|
| Brand | I-Line |
| Product Type | Hanger kit |

Dimensions

| | |
|-------------------------------------|----------------------|
| Nominal Size | 2-1/4 in |
| Compatible Diameter, maximum | 59.944 mm 2.360 in |
| Compatible Diameter, minimum | 58.166 mm 2.290 in |
| Height | 41.00 mm 1.61 in |
| Length | 104.00 mm 4.09 in |
| Width | 44.50 mm 1.75 in |

Electrical Specifications

| | |
|---------------------------|--------|
| DTF Effect | 0.1 dB |
| Return Loss Effect | 0.1 dB |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -40 °C to +85 °C (-40 °F to +185 °F) |
|------------------------------|--------------------------------------|

General Specifications

| | |
|--------------------------|-----------------|
| Hanger Type | Snap-in hanger |
| Cables per Hanger | 1 |
| Color | Silver |
| Material Type | Stainless steel |

| | |
|-------------------------|---------------------------------|
| Ordering Note | CommScope® non-standard product |
| Package Quantity | 10 |

Mechanical Specifications

| | |
|--|----------------------------------|
| Corrosion Resistance, minimum with no degradation | ≥500 hours in salt spray chamber |
| Mounting | 3/4 in drilled cable ladder |
| Vibration Survival | ≥4 hours at resonant frequency |
| Environmental Strength Capability | Double cable weight |

Packed Dimensions

| | |
|------------------------|-------------------|
| Height | 30.4 cm 12.0 in |
| Length | 6.3 cm 2.5 in |
| Shipping Weight | 0.80 kg 1.76 lb |
| Width | 27.9 cm 11.0 in |