



Butterfly Hanger for 2-1/4 in corrugated coaxial cable

**OBSOLETE**

This product was discontinued on: **October 1, 2013**

**Replaced By**

42396A-4

Butterfly Hanger for 2-1/4 in coaxial cable and elliptical waveguide 37

## Product Classification

<b>Brand</b>	I-Line
<b>Product Type</b>	Hanger kit

## Dimensions

<b>Nominal Size</b>	2-1/4 in
<b>Compatible Diameter, maximum</b>	59.944 mm   2.360 in
<b>Compatible Diameter, minimum</b>	58.166 mm   2.290 in
<b>Height</b>	82.00 mm   3.23 in
<b>Length</b>	110.00 mm   4.33 in
<b>Width</b>	38.10 mm   1.50 in

## Electrical Specifications

<b>DTF Effect</b>	0.1 dB
<b>Return Loss Effect</b>	0.1 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

## General Specifications

<b>Hanger Type</b>	Standard butterfly hanger
<b>Cables per Hanger</b>	1

<b>Color</b>	Silver
<b>Material Type</b>	Stainless steel
<b>Ordering Note</b>	CommScope® non-standard product
<b>Package Quantity</b>	10

## Mechanical Specifications

<b>Corrosion Resistance, minimum with no degradation</b>	≥500 hours in salt spray chamber
<b>Mounting</b>	3/8 in (M10) drilled cable ladder
<b>Vibration Survival</b>	≥4 hours at resonant frequency
<b>Environmental Strength Capability</b>	Double cable weight

## Packed Dimensions

<b>Height</b>	33.0 cm   13.0 in
<b>Length</b>	6.0 cm   2.4 in
<b>Shipping Weight</b>	0.74 kg   1.64 lb
<b>Width</b>	22.0 cm   8.7 in