



Cushion Hanger Assembly for 7/8 in corrugated coaxial cable, two holes

OBSOLETE

Product Classification

Brand	I-Line
Product Type	Hanger kit

Dimensions

Nominal Size	7/8 in
Compatible Diameter, maximum	30.988 mm 1.220 in
Compatible Diameter, minimum	26.670 mm 1.050 in
Height	25.40 mm 1.00 in
Length	96.00 mm 3.78 in
Width	79.75 mm 3.14 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

General Specifications

Hanger Type	Cushion hanger
Cables per Hanger	2
Color	Black
Material Type	Engineered plastic
Ordering Note	CommScope® non-standard product
Package Quantity	10

Mechanical Specifications

Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Mounting	3/8 in (M10) drilled cable ladder
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber
Vibration Survival	≥4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

Packed Dimensions

Height	17.0 cm 6.7 in
Length	10.0 cm 3.9 in
Shipping Weight	0.44 kg 0.96 lb
Width	13.0 cm 5.1 in