

## Butterfly Hanger for 1-1/4 in coaxial cable and elliptical waveguide 64



### Product Classification

**Product Type** Hanger kit

### Dimensions

<b>Nominal Size</b>	1-1/4 in
<b>Compatible Diameter, maximum</b>	43.180 mm   1.700 in
<b>Compatible Diameter, minimum</b>	37.592 mm   1.480 in
<b>Height</b>	59.00 mm   2.32 in
<b>Length</b>	76.20 mm   3.00 in
<b>Width</b>	38.10 mm   1.50 in

### Electrical Specifications

<b>DTF Effect</b>	0.1 dB
<b>Return Loss Effect</b>	0.1 dB

### Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

### General Specifications

<b>Hanger Type</b>	Standard butterfly hanger
<b>Cables per Hanger</b>	1
<b>Color</b>	Silver
<b>Material Type</b>	Stainless steel
<b>Ordering Note</b>	CommScope® standard product in the United States and Canada
<b>Package Quantity</b>	10

### Mechanical Specifications

<b>Corrosion Resistance, minimum with no degradation</b>	≥500 hours in salt spray chamber
<b>Mounting</b>	3/8 in (M10) drilled cable ladder

# 42396A-1

---

**Vibration Survival** ≥4 hours at resonant frequency  
**Environmental Strength Capability** Double cable weight

## Packed Dimensions

**Height** 26.0 cm | 10.2 in  
**Length** 9.0 cm | 3.5 in  
**Shipping Weight** 0.53 kg | 1.16 lb  
**Width** 9.0 cm | 3.5 in

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU  
ISO 9001:2015  
China RoHS SJ/T 11364-2014

### Classification

Compliant  
Designed, manufactured and/or distributed under this quality management system  
Below Maximum Concentration Value (MCV)

