

SnapStak® Hanger Kit for 3/8 in RET cable



Product Classification

Brand	SnapStak®
Product Type	Hanger kit

Dimensions

Nominal Size	3/8 in
Compatible Diameter, maximum	8.890 mm 0.350 in
Compatible Diameter, minimum	7.110 mm 0.280 in
Height	41.00 mm 1.61 in
Length	66.00 mm 2.60 in
Width	22.80 mm 0.90 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

General Specifications

Hanger Type	Snap-in hanger
Cables per Hanger	1
Color	Silver
Material Type	Stainless steel
Ordering Note	CommScope® non-standard product
Package Quantity	10

Mechanical Specifications

SSHAK-3812

Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Mounting	3/8 in (M10) drilled cable ladder
Vibration Survival	≥4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

Packed Dimensions

Height	32.5 cm 12.8 in
Length	15.5 cm 6.1 in
Shipping Weight	1.40 kg 3.09 lb
Width	13.5 cm 5.3 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

