



Cushion Insert with 1 hole for 7/8 in corrugated coaxial cable

## Product Classification

<b>Brand</b>	I-Line
<b>Product Type</b>	Cushion insert

## Dimensions

<b>Nominal Size</b>	7/8 in
<b>Height</b>	82.55 mm   3.25 in
<b>Length</b>	25.40 mm   1.00 in

## General Specifications

<b>Cable Type</b>	Corrugated
<b>Cables per Cushion</b>	1
<b>Color</b>	Black
<b>Includes</b>	Cushion
<b>Material Type</b>	EPDM rubber
<b>Ordering Note</b>	CommScope® non-standard product
<b>Package Quantity</b>	1

## Mechanical Specifications

<b>UV Resistance Test Method</b>	MIL-STD-810E, Procedure 11, Method 505
<b>UV Resistance, minimum with no degradation</b>	=1000 hours
<b>Weather Resistance Test Method</b>	04AS00-03.9.0   IEC 60529:2001, IP66

## Packed Dimensions

<b>Height</b>	169.9 mm   6.7 in
<b>Length</b>	99.8 mm   3.9 in
<b>Shipping Weight</b>	0.80 kg   1.76 lb
<b>Width</b>	129.8 mm   5.1 in