

## Self-locking Hanger for 1/2 in RCT4 RADIAX® Radiating cable



### Product Classification

**Product Type** Hanger kit

### Dimensions

<b>Nominal Size</b>	1/2 in
<b>Compatible Diameter, maximum</b>	16.800 mm   0.661 in
<b>Compatible Diameter, minimum</b>	14.300 mm   0.563 in
<b>Height</b>	32.00 mm   1.26 in
<b>Length</b>	20.60 mm   0.81 in
<b>Width</b>	17.10 mm   0.67 in

### Environmental Specifications

**Operating Temperature** -40 °C to +80 °C (-40 °F to +176 °F)

### General Specifications

<b>Hanger Type</b>	Self locking hanger
<b>Cables per Hanger</b>	1
<b>Color</b>	Black
<b>Material Type</b>	Polyamide PA12
<b>Maximum Stack Height</b>	2
<b>Package Quantity</b>	100

### Mechanical Specifications

<b>Flammability Test Method</b>	UL 94-HB
<b>Maximum Load</b>	650 N   146 lbf
<b>Toxicity Index Test Method</b>	IEC 60754-2
<b>UV Resistance, minimum with no degradation</b>	≥500 hours exposure in accelerated UV life chamber

# 209800-15B

---

## Packed Dimensions

<b>Height</b>	10.0 cm   3.9 in
<b>Length</b>	18.0 cm   7.1 in
<b>Shipping Weight</b>	0.50 kg   1.10 lb
<b>Width</b>	11.5 cm   4.5 in

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power