

Self-locking Hanger for 7/8 in RCT5 RADIAX® Radiating cable



Product Classification

Product Type Hanger kit

Dimensions

Nominal Size	7/8 in
Compatible Diameter, maximum	27.800 mm 1.094 in
Compatible Diameter, minimum	24.600 mm 0.969 in
Height	45.10 mm 1.78 in
Length	30.40 mm 1.20 in
Width	20.00 mm 0.79 in

Environmental Specifications

Operating Temperature -40 °C to +80 °C (-40 °F to +176 °F)

General Specifications

Hanger Type	Self locking hanger
Cables per Hanger	1
Color	Black
Material Type	Polyamide PA12
Maximum Stack Height	2
Package Quantity	50

Mechanical Specifications

Flammability Test Method	UL 94-HB
Maximum Load	900 N 202 lbf
Toxicity Index Test Method	IEC 60754-2
UV Resistance, minimum with no degradation	=500 hours exposure in accelerated UV life chamber

Packed Dimensions

Height	10.0 cm 3.9 in
Length	18.0 cm 7.1 in
Shipping Weight	0.51 kg 1.12 lb
Width	11.5 cm 4.5 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power