



Self-locking Hanger for 1-5/8 in RADIAX® Radiating cable

Product Classification

Product Type Hanger kit

Dimensions

Nominal Size 1-5/8 in
Compatible Diameter, maximum 50.500 mm | 1.988 in
Compatible Diameter, minimum 46.500 mm | 1.831 in
Height 72.80 mm | 2.87 in
Length 53.50 mm | 2.11 in
Width 22.00 mm | 0.87 in

Environmental Specifications

Operating Temperature -40 °C to +80 °C (-40 °F to +176 °F)

General Specifications

Hanger Type Self locking hanger
Cables per Hanger 1
Color Black
Material Type Polyamide PA12
Maximum Stack Height 2
Package Quantity 25

Mechanical Specifications

Flammability Test Method UL 94-HB
Maximum Load 1400 N | 315 lbf
Toxicity Index Test Method IEC 60754-2
UV Resistance, minimum with no degradation ≥500 hours exposure in accelerated UV life chamber

Packed Dimensions

Height	11.5 cm 4.5 in
Length	30.0 cm 11.8 in
Shipping Weight	2.10 kg 4.63 lb
Width	8.5 cm 3.3 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power