



Round Base, 45 mm stand-off, for RCT RADIAX® Coupling Mode Radiating cable

Product Classification

Brand RADIAX®
Product Type Base

Dimensions

Height 45.00 mm | 1.77 in
Length 45.00 mm | 1.77 in
Width 45.00 mm | 1.77 in

Environmental Specifications

Operating Temperature -40 °C to +80 °C (-40 °F to +176 °F)

General Specifications

Adapter Type Stand-off adapter
Color Black
Material Type Polyamide PA6
Ordering Note CommScope® non-standard product
Package Quantity 100

Mechanical Specifications

Flammability Test Method UL 94 V-0
Toxicity Index Test Method IEC 60754-2
UV Resistance, minimum with no degradation ≥500 hours exposure in accelerated UV life chamber

Packed Dimensions

Height 19.5 cm | 7.7 in
Length 30.5 cm | 12.0 in
Shipping Weight 2.46 kg | 5.42 lb
Width 13.5 cm | 5.3 in

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

