

Universal Snap-in Hanger for 2-1/4 in corrugated coaxial cable



OBSOLETE

Product Classification

Product Type Hanger kit

Dimensions

Nominal Size 2-1/4 in
Compatible Diameter, maximum 52.070 mm | 2.050 in
Compatible Diameter, minimum 48.260 mm | 1.900 in
Height 41.00 mm | 1.61 in
Length 90.00 mm | 3.54 in
Width 60.00 mm | 2.36 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type Snap-in hanger
Cable Type Corrugated
Cables per Hanger 1
Color Silver
Material Type Stainless steel
Ordering Note CommScope® non-standard product
Package Quantity 10

Mechanical Specifications

| | |
|--|-----------------------------------|
| Corrosion Resistance, minimum with no degradation | ≥500 hours in salt spray chamber |
| Mounting | 3/8 in (M10) drilled cable ladder |
| Vibration Survival | ≥4 hours at resonant frequency |
| Environmental Strength Capability | Double cable weight |

Packed Dimensions

| | |
|------------------------|-------------------|
| Height | 17.0 cm 6.7 in |
| Length | 10.0 cm 3.9 in |
| Shipping Weight | 0.71 kg 1.57 lb |
| Width | 13.0 cm 5.1 in |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

