

Butterfly Hanger for elliptical waveguide 17



Product Classification

Product Type Hanger kit

Dimensions

Height 76.20 mm | 3.00 in

Waveguide Size EW17

Electrical Specifications

DTF Effect 0.1 dB

Return Loss Effect 0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type Standard butterfly hanger

Cable Type Elliptical waveguide

Cables per Hanger 1

Color Silver

Material Type Stainless steel

Ordering Note CommScope® non-standard product

Package Quantity 10

Mechanical Specifications

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Mounting 3/8 in (M10) drilled cable ladder

Vibration Survival ≥4 hours at resonant frequency

Environmental Strength Capability Double cable weight

Packed Dimensions

31766A-9

Height	47.0 cm 18.5 in
Length	10.8 cm 4.3 in
Shipping Weight	2.23 kg 4.92 lb
Width	10.8 cm 4.3 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

