

## Single Entrance Panel for elliptical waveguide 240



### Product Classification

**Product Type** Entrance panel

### Dimensions

**Height** 76.20 mm | 3.00 in  
**Waveguide Size** WR42 | WG20 | R220  
**Width** 127.00 mm | 5.00 in

### General Specifications

**Number of Ports** 1  
**Panel Type** Single  
**Color** Gray  
**Entry Panel Port Size** 101.6 mm | 4.0 in  
**Includes** Boot | Plate  
**Material Type** Aluminum  
**Package Quantity** 1

### Mechanical Specifications

**Weather Resistance Test Method** 04AS00-03.9.0 | IEC 60529.14.2

### Packed Dimensions

**Height** 180.0 mm | 7.1 in  
**Length** 180.0 mm | 7.1 in  
**Shipping Weight** 0.91 kg | 2.01 lb  
**Width** 180.0 mm | 7.1 in

### Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## Included Products

204673-1 — 1 Port Entrance Panel 1 x 1

- CAP-4 — Snap-in Entry Port Cap, 4 in

WGB4-240 — Boot Assembly, 4 in, for elliptical waveguide 240



1 Port Entrance Panel 1 x 1

## Product Classification

**Product Type** Entrance panel

## Dimensions

**Height** 177.80 mm | 7.00 in

**Width** 177.80 mm | 7.00 in

## General Specifications

**Number of Ports** 1  
**Panel Type** Single  
**Color** Gray  
**Entry Panel Port Size** 101.6 mm | 4.0 in  
**Includes** Entry cap | Hardware | Port  
**Material Type** Aluminum  
**Ordering Note** CommScope® non-standard product  
**Package Quantity** 1

## Mechanical Specifications

**Weather Resistance Test Method** 04AS00-03.9.0 | IEC 60529:2001, IP66

## Packed Dimensions

**Height** 177.8 mm | 7.0 in

**Length** 40.6 mm | 1.6 in

**Shipping Weight** 0.28 kg | 0.62 lb

**Width** 177.8 mm | 7.0 in

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## Included Products

CAP-4 — Snap-in Entry Port Cap, 4 in

# WGB4-240

---



Boot Assembly, 4 in, for elliptical waveguide 240

## Product Classification

**Product Type** Boot assembly

## Dimensions

**Length** 76.20 mm | 3.00 in  
**Waveguide Size** WR42 | WG20 | R220  
**Width** 101.60 mm | 4.00 in

## General Specifications

**Cable Type** Elliptical waveguide  
**Cables per Cushion** 1  
**Color** Black  
**Includes** Boot | Cushion  
**Material Type** EPDM rubber  
**Package Quantity** 1

## Mechanical Specifications

**UV Resistance Test Method** MIL-STD-810E, Procedure 11, Method 557  
**Weather Resistance Test Method** 04AS00-03.9.52 | IEC 60529:2001, IP66

## Regulatory Compliance/Certifications

**Agency** ISO 9001:2015  
**Classification** Designed, manufactured and/or distributed under this quality management system

