



Angle Adapter, compact 1/4 in tapped hole

## Product Classification

**Product Type** Adapter

## Dimensions

<b>Inside Length</b>	16.00 mm   0.63 in
<b>Inside Width</b>	16.51 mm   0.65 in
<b>Outside Length</b>	44.45 mm   1.75 in
<b>Outside Width</b>	21.59 mm   0.85 in

## General Specifications

<b>Adapter Type</b>	Angle adapter
<b>Material Type</b>	Zinc-plated steel
<b>Ordering Note</b>	CommScope® non-standard product
<b>Package Quantity</b>	10

## Mechanical Specifications

<b>Installation Torque, maximum</b>	12.0 ft lb
<b>Installation Torque, minimum</b>	10.0 ft lb
<b>Material Thickness</b>	2.337 mm   0.092 in
<b>Maximum Loading</b>	Single, 1-5/8 in cable
<b>Mounting</b>	1/4 in tapped hole

## Packed Dimensions

<b>Height</b>	2.5 cm   1.0 in
<b>Length</b>	20.3 cm   8.0 in
<b>Shipping Weight</b>	0.69 kg   1.52 lb
<b>Width</b>	12.7 cm   5.0 in

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

**Classification**

Compliant

Designed, manufactured and/or distributed under this quality management system

Below Maximum Concentration Value (MCV)

