

# SHK-19-1-PV2



Hanger Kit for single stack of RFA812 cable; includes ten sets of hardware, angle adapters

## Product Classification

<b>Brand</b>	HELIAX®
<b>Product Type</b>	Hanger kit

## Dimensions

<b>Compatible Diameter, maximum</b>	19.558 mm   0.770 in
<b>Compatible Diameter, minimum</b>	20.066 mm   0.790 in
<b>Length</b>	104.00 mm   4.09 in

## Electrical Specifications

<b>DTF Effect</b>	0.1 dB
<b>Return Loss Effect</b>	0.1 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

## General Specifications

<b>Hanger Type</b>	Composite clamp
<b>Cables per Hanger</b>	1
<b>Color</b>	Black
<b>Includes</b>	Angle adapter   Hardware
<b>Material Type</b>	Engineered plastic   Stainless steel
<b>Maximum Stack Height</b>	1
<b>Package Quantity</b>	10

## Mechanical Specifications

<b>Corrosion Resistance, minimum with no degradation</b>	≥500 hours in salt spray chamber
<b>Mounting</b>	M8 hardware

# SHK-19-1-PV2

---

<b>UV Resistance, minimum with no degradation</b>	≥100 hours exposure in accelerated UV life chamber
<b>Vibration Survival</b>	≥4 hours at resonant frequency
<b>Environmental Strength Capability</b>	Double cable weight

## Packed Dimensions

**Shipping Weight** 2.80 kg | 6.17 lb

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power