

FA-1923-STH



Standard Butterfly Hanger and Grommet kit for HELIAX® FiberFeed® Cables, 19-23mm

Product Classification

Product Type Hanger kit

Dimensions

Nominal Size 1-1/4 in
Compatible Diameter, maximum 23.000 mm | 0.906 in
Compatible Diameter, minimum 19.000 mm | 0.748 in
Height 59.00 mm | 2.32 in
Length 76.20 mm | 3.00 in
Width 38.10 mm | 1.50 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type Hanger kits
Cables per Hanger 1
Color Black | Silver
Material Type Stainless steel
Package Quantity 10

Mechanical Specifications

Corrosion Resistance, minimum with no degradation =500 hours in salt spray chamber
Mounting 3/8 in (M10) drilled cable ladder
Vibration Survival =4 hours at resonant frequency
Environmental Strength Capability Double cable weight

FA-1923-STH

Packed Dimensions

Height	26.0 cm 10.2 in
Length	9.0 cm 3.5 in
Shipping Weight	0.53 kg 1.16 lb
Width	9.0 cm 3.5 in

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

Below Maximum Concentration Value (MCV)

